

Waterbath

Model WNB 29

Standard equipment

Control

- microprocessor PID-temperature controller with integrated autodiagnostic system with fault indicator
- solid state switching unit
- one Pt100 sensor class A in 4-wire-circuit
- integrated digital timer from 1 min. to 99,59 hours for: ON continuous operation WAIT (delayed on for continuous and limited timed operation) HOLD
- digital display (LED) of set and actual temperature (0,1 ℃ resolution) and of (remaining) programme time
- LEDs for indication of programme status

Overtemperature protection (double)

- in case of overtemperature due to failure, the heating is switched off at approx. 10 ℃ above the set temperature (fixed value)
- mechanical temperature limiter TB protection class 1 switching the heating off at approx. 30 °C above max. temperature of the bath

Textured Stainless Steel Casing

- I x w x h: 818 x 516 x 238 mm
- material 1.4301, corrosion resistant

Interior - Heating Concept

- I x w x h: 590 x 350 x 140 mm, 29 l
- easy-to-clean interior, made of stainless steel, reinforced by deep drawn ribbing, material no. 1.4301, laser-welded
- corrosion-proof large-area heating on three sides



Temperature Range

 from +10 ℃ (however, at least 5 ℃ above ambient) up to +95 ℃ with additional boiling mode (+100 ℃)

Voltage / Power Rating

- 230 V (+/- 10%), 50/60 Hz
- ca. 2.400 W (during heating)

Packing Data

- net weight approx. 22 kg
- gross weight carton approx. 29 kg
- gross weight wooden case approx. 43 kg
- dimensions approx.: carton w x h x d: 91 x 61 x 40 cm wooden case w x h x d: 94 x 64 x 46 cm
- the appliances must be transported upright

Customs Tariff Number

• 8419 3990

Country of Origin

• Federal Republic of Germany

WEEE-Reg.-No.

• DE 66812464

Accessories

- Flat stainless steel cover with openings and concentric ring sets (8 openings / 107 mm diameter)
- Flat stainless steel cover with openings and concentric ring sets (4 openings / 187 mm diameter)
- Gable stainless steel cover mounted L1
 for condensate drainage
- Water level control (for WNB, WNE, L3

WPE)